



KA44

by Burndy
Catalog ID: KA44

Prop 65 Notice

Terminal, Use on for Copper Cable.

Compact and economical

Product Details

General

Application	Capable of joining wide range of cables to equipment pad or terminal block
Connector Type	Terminal
Hardware Type	1 1/8 UNF Hex SetScrew
Material	Copper
Material - Hardware	Stainless Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Type	Bolted Lugs & Terminals
UPC	781810252031

Dimensions

Dimension - B Length fraction	1-13/25 in
Dimension - B Length inch	1.52 in
Dimension - D inch	2.36 in
Dimension - Height fraction	2 in
Dimension - Height inch	2.00 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.88 in
Dimension - N inch	0.67 in
Dimension - Pad Width inch	1.75 in

Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	250 kcmil-800 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)