



KA8CH

by Burndy
Catalog ID: KA8CH

#14 Solid - #8 Stranded Copper; #10 Stud; 45 in-lb recommended torque

Product Details

General

Connector Type	Terminal
Material	Copper
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	KA-LUG™
Type	Bolted Lugs & Terminals
UPC	781810528358
UPC 12 Digit	7818105283588

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)