



## KAP350

by Burndy  
Catalog ID: KAP350

Prop 65 Notice

350 kcmil pin adaptor, Torque: 100 N lb, Voltage: 600 V.

- AL9CU Dual Rated for both copper an aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range Taking conductor port
- Plastisol insulated covers provided with each connector

AL9CU- UL Listed for use with fine strand conductor

## Product Details

### General

Application	Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.
Hex Key	3/8 in
Installation Torque Recommended in-lb	450
Sub Brand	Pin Adaptor
Type	1/0 - 350 Mechanical Pin Adaptor; Centered Pin
UPC	621945493339

### Dimensions

Dimension - Strip Length inch	1.11 in
Height	2.00 in
Length	2.75 in
Outside Diameter	1.38 in
Width	1.50 in

### Electrical Ratings

Amperage Rating	350 A
-----------------	-------

### Conductor Related

Conductor - AL Str Size Range	#6 - 1/0 AWG
Conductor - Copper DLO Size Range	#6 - 1/0 AWG
Conductor - Copper Flex H Size Range	#6 - 1/0 AWG
Conductor - Copper Flex I Size Range	#6 - 1/0 AWG
Conductor - Copper Flex K Size Range	#6 - 1/0 AWG
Conductor - Copper Str Size Range	#6 - 1/0 AWG

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)