

KAUKIT3

by Burndy
Catalog ID: KAUKIT3

Prop 65 Notice

Transformer Lug Kit, #6 - 350 kcmil 300 - 800 kcmil.

Features: These Dual-Rated Lugs Are Constructed From High Strength Aluminum Alloy And Electro Tinned To Provide Low Contact Resistance, Lugs And Mounting Hardware Packaged Together In These Kits, UL Listed AL9CU Dual Rated Set Screw Terminals And CSA Certified, Ensure The Transformer Feeders And Taps Are Terminated Properly, Plated Steel Cap Screws And Hex Nuts With Captive Conical Washers Or Individual Belleville Washers, Terminal To Bus Connections Are Made Using Proper Hardware Resulting In True Torque To Pressure Performance, Compensates For Dissimilar Metal Expansion And Contraction, Hardware Packed In Plastic Bag, No Lost Hardware Prior To Installation, Includes: (5) 1/2-13 X 2 IN, (6) 1/2-13 X 2-1/2 IN, (11) 1/2-13 Hex Head, (6) K2A31U, (7) K2A40U Terminal, (11) 1/2 IN Belleville Washer, (22) 1/2 IN Flatwasher, Conductor Type: Run: Stranded Aluminum Or Copper, Transformer Kva Rating Range: 100 - 167 KVA For Single Phase, 150 - 300 KVA For Three Phase



Product Details

General

Application	used to provide low contact resistance
Material	Aluminum
Sub Brand	UNIVERSAL TERM
Type	Bolted Lugs & Terminals
UPC	781810600139

Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
-------------------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	(6) K2A31U, (7) K2A40U;(5) 1/2-13 x 2 in, (6) 1/2-13 x 2-1/2 in Hex Bolts;(11) 1/2-13 Hex Head Nuts;(22) 1/2 in Flatwashers;(11) 1/2 in Belleville Washers

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)