



## KC15B1

by Burndy  
Catalog ID: KC15B1

Prop 65 Notice

Mechanical Grounding Connector, Cable to Flat, 12 - 9 AWG (Str) / 12 - 8 AWG (Sol), 1/4" Stud

## Product Details

### General

Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	80 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810254158
UPC 12 Digit	7818102541588

### Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.87 in
Dimension - Body Width inch	0.38 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	1.00 in
Dimension - Height fraction	5/8
Dimension - Height inch	0.69 in
Dimension - L Length Overall mm	42.9 mm
Dimension - Length Overall inch	1.69 in
Dimension - Nut Width inch	0.50 in
Dimension - P inch	0.14 in
Dimension - Threads per inch	20

### Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Solid Size Range	12 AWG-8 AWG
Conductor - Copper Str Size	12 AWG;10 AWG;9 AWG
Conductor - Copper Str Size Range	12 AWG-9 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)