



KC20NSP

by Burndy
Catalog ID: KC20NSP

Prop 65 Notice

#10 - #5 AWG Stranded Copper or #10 - #4 AWG Solid Copper; Supplied with split lock washer and nut

Product Details

General

Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	180 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810433744
UPC 12 Digit	7818104337444

Dimensions

Dimension - B Length inch	0.41 in
Dimension - Body Width inch	0.50 in
Dimension - D inch	0.63 in
Dimension - Height inch	0.86 in
Dimension - L Length Overall mm	36 mm
Dimension - Length Overall inch	1.42 in
Dimension - Nut Width inch	0.69 in
Dimension - P inch	0.22 in

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	4 AWG-10 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG
Conductor - Copper Str Size Range	5 AWG-10 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)