



KC22TN

by Burndy
Catalog ID: KC22TN

Prop 65 Notice

Mechanical Grounding Connector, NUT TORQUE 275 LBS, STUD TORQUE 280 LBS

Product Details

General

Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Leaded Bronze Alloy
Stud Installation Torque inch pounds	280 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810210161
UPC 12 Digit	7818102101611

Dimensions

Dimension - B Length inch	0.46 in
Dimension - Body Width inch	0.62 in
Dimension - D inch	0.63 in
Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.62 in
Dimension - Nut Width inch	0.75 in
Dimension - P inch	0.26 in
Dimension - Width inch	25 mm

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	2 AWG-10 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG
Conductor - Copper Str Size Range	3 AWG-10 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)