



KC26NSP

by Burndy
Catalog ID: KC26NSP

Prop 65 Notice

Cu Mechanical ground conctr to ground 2 Cables to Steel structures, #2-2/0 Str., #2-3/0 Sol., Connector supplied with Split lock washer and nut

Product Details

General

Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	480 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810339190
UPC 12 Digit	7818103391900

Dimensions

Dimension - B Length inch	0.52 in
Dimension - Body Width inch	0.88 in
Dimension - D inch	0.75 in
Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.12 in
Dimension - Nut Width inch	1.04 in
Dimension - P inch	0.44 in

Conductor Related

Conductor - Copper Solid Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Size Range	2 AWG-3/0 AWG
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	2 AWG-2/0 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)