



## KC28B1G16

by Burndy  
Catalog ID: KC28B1G16

Prop 65 Notice

3/8"-16

## Product Details

### General

Material	Bronze Alloy, Leaded
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	280 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810276181
UPC 12 Digit	7818102761811

### Dimensions

Dimension - B Length inch	1.25 in
Dimension - Body Width inch	1.18 in
Dimension - Height inch	1.94 in
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.45 in
Dimension - Nut Width inch	1.35 in
Dimension - P inch	0.55 in

### Conductor Related

Conductor - Copper Solid Size	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	1 AWG-4/0 AWG
Conductor - Copper Str Size	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1 AWG-4/0 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)