



KC28B1N

by Burndy
Catalog ID: KC28B1N

Prop 65 Notice

Mechanical Grounding Connector, NUT TORQUE 500 LBS, POST TORQUE 660 LBS

Product Details

General

Material	Copper Alloy, Cast
Plated	N
Plating Type	Unplated
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC 12 Digit	0

Conductor Related

Conductor - Copper Solid Size Range	1 AWG-4/0 AWG
Conductor - Copper Str Size Range	1 AWG-4/0 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)