



## KC34B1NSP

by Burndy  
Catalog ID: KC34B1NSP

Prop 65 Notice

Mechanical Grounding Connector, NUT TORQUE 825 LBS, STUD TORQUE 1050 LBS

## Product Details

### General

Material	Copper Alloy, Cast
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	1050 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810219881
UPC 12 Digit	7818102198811

### Dimensions

Dimension - Body Width inch	1.62 in
Dimension - Length Overall inch	4.12 in
Dimension - Nut Width inch	2.00 in
Dimension - P inch	0.85 in

### Conductor Related

Conductor - Copper Str Size	1;1/0;2/0;3/0;4/0;250;300
Conductor - Copper Str Size Range	1-300
Physical Attribute - Number of Conductors Accommodated Total	1

### Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)