



KC34J12T13

by Burndy
Catalog ID: KC34J12T13

Prop 65 Notice

Mechanical Grounding Connector, NUT TORQUE 825 LBS, STUD TORQUE 1050 LBS

Product Details

General

Installation Torque Recommended in-lb	1050 LBS/in
Material	Copper Alloy, Cast
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	1050 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810135280
UPC 12 Digit	7818101352800

Dimensions

Dimension - Body Width inch	1.62 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	3.62 in
Dimension - Nut Width inch	2.00 in
Dimension - P inch	0.85 in
Dimension - Threads per inch	13

Conductor Related

Conductor - Copper Str Size	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	3/0 AWG-500 Kcmil
Physical Attribute - Number of Conductors Accommodated Total	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)