



KC34W

by Burndy
Catalog ID: KC34W

Hot tin dipped; 3/0 Stranded - 500 kcmil; 3/4" Stud

Product Details

General

Material	Copper Alloy, Cast
Plated	Y
Plating Type	Tin - Hot Dipped
Stud Installation Torque inch pounds	1050 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC 12 Digit	0

Dimensions

Dimension - B Length inch	0.99 in
Dimension - Body Width inch	1.62 in
Dimension - Height inch	2.38 in
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.62 in
Dimension - Nut Width inch	2.00 in
Dimension - P inch	0.85 in

Conductor Related

Conductor - Copper Str Size	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Physical Attribute - Number of Conductors Accommodated Total	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)