



KCKF23

by Burndy
Catalog ID: KCKF23

Prop 65 Notice

BulkHead Servit, #8 - #2 AWG STR, #10 - #1 AWG Sol , Nut Torque- 275 Lbs.

Features: The Bulkhead connector is designed to allow a ground wire to be connected from the inside of a box or enclosure to the outside of a box or enclosure, SPLIT WASHER AND FLAT WASHER: STAINLESS STEEL SEALING WASHER: NEOPRENE

Product Details

General

Application	Designed to allow a ground wire to be connected from the inside of a box or enclosure to the outside of a box or enclosure
Material	Copper
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	100 LBS/in
Sub Brand	SERVIT POST
Trade Name	SERVIT POST™
Type	Bulkhead Servit
UPC	781810567432
UPC 12 Digit	7818105674322

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Size Range	10 AWG-1 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)