



KCKF25

by Burndy
Catalog ID: KCKF25

Prop 65 Notice

BulkHead Servit, #2 - 1/0 AWG STR, #2 - #2/0 AWG Sol, Nut Torque- 385 Lbs.

Features: The Bulkhead connector is designed to allow a ground wire to be connected from the inside of a box or enclosure to the outside of a box or enclosure, SPLIT WASHER AND FLAT WASHER: STAINLESS STEEL SEALING WASHER: NEOPRENE

Product Details

General

| | |
|--------------------------------------|--|
| Application | Designed to allow a ground wire to be connected from the inside of a box or enclosure to the outside of a box or enclosure |
| Material | Copper |
| Plated | N |
| Plating Type | Unplated |
| Stud Installation Torque inch pounds | 150 LBS/in |
| Sub Brand | SERVIT POST |
| Trade Name | SERVIT POST™ |
| Type | Bulkhead Servit |
| UPC | 781810567449 |
| UPC 12 Digit | 7818105674499 |

Conductor Related

| | |
|-------------------------------------|-----------------------------|
| Conductor - Copper Solid Size | 2 AWG;1 AWG;1/0 AWG;2/0 AWG |
| Conductor - Copper Solid Size Range | 2 AWG-2/0 AWG |
| Conductor - Copper Str Size | 2 AWG;1 AWG;1/0 |
| Conductor - Copper Str Size Range | 2 AWG-1/0 AWG |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | UI |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)