



## KK6A34U8

by Burndy  
Catalog ID: KK6A34U8

Prop 65 Notice

6 Conductors #2 AWG - 500 kcmil; Dual Rated

## Product Details

### General

Connector Type	Terminal
Finish Type	Clear Plate Cms-14
Material	Aluminum
Physical Attribute - Number of Holes	8
Plated	Y
Plating Type	Clear plated
Type	Bolted Lugs & Terminals
UPC	781810666654

### Dimensions

Dimension - Height inch	1.5 in
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.75 in
Dimension - Stud Size fraction	9/16

### Conductor Related

Conductor - AL Str Size Range	10 Str. - 500 Kcmil
Conductor - Copper Str Size Range	10 Str. - 500 Kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• AL C Str-Size</li> </ul>
Number Of Conductors	6
Number Of Wires	6

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	12 EA
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)