



KLU125TP

by Burndy
Catalog ID: KLU125TP

Cu Alloy Scrulug (Offset Pad Term Lug), #2-1/0 AWG (STR), 1/4 IN Stud, , 1.99 IN L,

Product Details

General

Connector Type	Terminal
Hardware Type	3/8 UNF Slotted SetScrew
Installation Torque Recommended in-lb	50
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810352656

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.61 in
Dimension - Hole Size inch	0.26 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.98 in
Dimension - N inch	0.42 in
Dimension - Pad Width inch	0.62
Dimension - Screw Size inch	3/8
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	2 AWG-1/0
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1500
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)