



KLU225CG5

by Burndy
Catalog ID: KLU225CG5

Prop 65 Notice

Copper Terminal, Offset Tongue, 1 Hole, 2-4/0 AWG (Str), 1/2" Stud, 1 Screw.

Product Details

General

| | |
|---------------------------------------|--------------------------|
| Connector Type | Terminal |
| Hardware Type | 7/16 UNF Socket/HexScrew |
| Installation Torque Recommended in-lb | 204 LBS/in |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Number of Screws | 1 |
| Physical Attribute - Screw Type | Allen |
| Plated | N |
| Plating Type | Unplated |
| Temperature Rating | 194 |
| Trade Name | SCRULUG™ |
| Type | Bolted Lugs & Terminals |
| UPC | 621945234994 |
| UPC 12 Digit | 6219452349944 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - B Length fraction | 67/87 in |
| Dimension - B Length inch | 0.77 in |
| Dimension - Hole Size inch | 0.33 in |
| Dimension - Hole Size mm | 8 mm |
| Dimension - L Length Overall mm | 65 mm |
| Dimension - Length Overall inch | 2.56 in |
| Dimension - N inch | 0.51 in |
| Dimension - Pad Width inch | 0.99 in |
| Dimension - Strip Length inch | 1 5/16 |
| Dimension - Stud Size inch | 5/16 |

Electrical Ratings

| | |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

Conductor Related

| | |
|-----------------------------|--|
| Conductor - Copper Str Size | 2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG |
|-----------------------------|--|

| | |
|-----------------------------------|---------------|
| Conductor - Copper Str Size Range | 2 AWG-4/0 AWG |
|-----------------------------------|---------------|

Certifications and Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)