



## KLU25TP

by Burndy  
Catalog ID: KLU25TP

WIRE: 14 SOL - 10 SOL CU STUD: 1/8 HARDWARE: #8-32  
SLOT/ROBERTSON TORQUE: 20 LB-IN STRIP LG: 7/16"

## Product Details

### General

|                                       |                                      |
|---------------------------------------|--------------------------------------|
| Connector Type                        | Terminal                             |
| Hardware Type                         | No. 8-32 Slotted Round Machine Screw |
| Installation Torque Recommended in-lb | 20                                   |
| Material                              | Copper                               |
| Physical Attribute - Number of Holes  | 1                                    |
| Physical Attribute - Number of Screws | 1                                    |
| Physical Attribute - Screw Type       | Slot                                 |
| Plated                                | Y                                    |
| Plating Type                          | Tin                                  |
| Trade Name                            | SCRULUG™                             |
| Type                                  | Bolted Lugs & Terminals              |
| UPC                                   | 781810352502                         |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length fraction   | 9/32 in |
| Dimension - B Length inch       | 0.28 in |
| Dimension - Hole Size inch      | 0.14 in |
| Dimension - Hole Size mm        | 4 mm    |
| Dimension - L Length Overall mm | 26 mm   |
| Dimension - Length Overall inch | 1.02 in |
| Dimension - N inch              | 0.21 in |
| Dimension - Pad Width inch      | 0.31 in |
| Dimension - Screw Size inch     | 8-32    |
| Dimension - Strip Length inch   | 7/16    |
| Dimension - Stud Size inch      | #6      |

### Conductor Related

|                                     |                                    |
|-------------------------------------|------------------------------------|
| Conductor - Copper Solid Size       | 14 AWG;13 AWG;12 AWG;11 AWG;10 AWG |
| Conductor - Copper Solid Size Range | 14 AWG-10 AWG                      |
| Conductor - Copper Str Size         | 14 AWG;12 AWG;10 AWG               |
| Conductor - Copper Str Size Range   | 14 AWG-10 AWG                      |

|                |  |
|----------------|--|
| Conductor Type | <ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul> |
|----------------|--|

## Certifications and Compliance

|   |       |
|---|-------|
| Certification - CSA Approved            | No    |
| Certification - ETL                     | No    |
| Certification - UL Listed Direct Burial | No    |
| Certification - UL Recognized           | No    |
| Certification - cULus                   | Yes   |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | CM    |
| UL Listed                               | No    |

## Logistics

|                       |        |
|-----------------------|--------|
| Carton Quantity       | 500 EA |
| Minimum Pack Quantity | 5000   |

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)