



KLU25

by Burndy
Catalog ID: KLU25

Prop 65 Notice

Copper Terminal, Offset Tongue, 1 Hole, 14-10 AWG (Sol), #6 Stud, 1 Screw.

Features: Terminal With Offset Tongue For Joining A Wide Range Of Cable To Equipment Pads Or Bar, Convenient Range-Taking Design, Reduces Catalog Numbers, One Conductor Accommodates Several Conductor Sizes, High Conductivity Copper Alloy, Long Lasting Reliable Contact, Compact Design, Easy To Use, Reduces Labor Time, Slot Robertson Screw, Hex Head/Hex Socket Bolt, No Special Installation Tools Required, Eliminates Over-Torquing/Potential Conductor Damage, Dimension N: 0.21 IN, Dimension K: 0.14 IN, Wire Strip Length: 7/16 IN, Dimension B: 0.26 IN, Dimension T: 07 IN, Set Screw Type: Slot Robertson, Tongue Width: 0.31 IN, Length: 12 IN, Stud/bolt Hole Size: #8, Installation Torque: 20 IN-LB

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar And Offset Tongue, Non-Plated
Connector Type	Terminal
Hardware Type	No. 8-32 Slotted Round Machine Screw
Installation Torque Recommended in-lb	20
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810351369

Dimensions

Dimension - B Length fraction	9/32 in
Dimension - B Length inch	0.28 in
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4 mm
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - N inch	0.21 in
Dimension - Pad Width inch	0.31 in
Dimension - Screw Size inch	8-32

Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	#6

Conductor Related

Conductor - Copper Solid Size	14;13;12;11;10
Conductor - Copper Solid Size Range	14-10
Conductor - Copper Str Size	14;12;10
Conductor - Copper Str Size Range	14-10
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)