



KLU70TP

by Burndy
Catalog ID: KLU70TP

Prop 65 Notice

WIRE: 8-2 CU STUD: 5/16" UNF Slotted screw, Stud hole: 1/4", TORQUE:
40 LB IN STRIP LG: 3/4"

Product Details

General

Connector Type	Terminal
Hardware Type	5/16 UNF Slotted SetScrew
Installation Torque Recommended in-lb	40
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810352601

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Hole Size inch	0.26 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.55 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.47 in
Dimension - Screw Size inch	5/16
Dimension - Strip Length inch	3/4
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG

Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	3000

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)