



## KPA25G8

by Burndy  
Catalog ID: KPA25G8

Prop 65 Notice

Cu Terminal, For Cu Cable, 1 Hole, #4-1/0 Str Commercial, 50-100 Navy, 5/16" Stud

### Product Details

#### General

Connector Type	Terminal
Installation Torque Recommended in-lb	180
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810035542

#### Dimensions

Dimension - D inch	0.81 in
Dimension - Height fraction	1-1/4 in
Dimension - Height inch	1.25 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.70 in
Dimension - N inch	0.41 in
Dimension - Pad Width inch	0.75 in

#### Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Navy-Size</li> </ul>

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)