



KPA25UNPL

by Burndy
Catalog ID: KPA25UNPL

Cu Unplated Terminal, 1 Hole, #4-1/0 Str, 5/16" Stud, 1 Screw

Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	180
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810172704

Dimensions

Dimension - D inch	0.81 in
Dimension - Height fraction	1-1/4 in
Dimension - Height inch	1.25 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.82 in
Dimension - N inch	0.41 in
Dimension - Pad Width inch	0.75 in
Dimension - Stud Size inch	5/16

Conductor Related

Conductor - Copper Str Navy Size	50 (19) Navy;60 (37) Navy;75 (37) Navy;100 (61) Navy
Conductor - Copper Str Navy Size Range	50 (19) Navy-100 (61) Navy
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	4 AWG-1/0
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Navy-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)