



KPA28CG1

by Burndy
Catalog ID: KPA28CG1

Copper Alloy Scrulug, #6 AWG - 4/0 Str. Copper; 9/16" Hex

Product Details

General

| | |
|---------------------------------------|-------------------------|
| Connector Type | Terminal |
| Hardware Type | 9/16 Hex SetScrew |
| Installation Torque Recommended in-lb | 28 |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Number of Screws | 1 |
| Physical Attribute - Screw Type | Hexagonal Bolt |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Type | Bolted Lugs & Terminals |
| UPC | 621945019324 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - D inch | 1.10 in |
| Dimension - Hole Size inch | 0.41 in |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 56 mm |
| Dimension - Length Overall inch | 2.22 in |
| Dimension - N inch | 0.57 in |
| Dimension - Pad Width inch | 1.00 in |
| Dimension - Width mm | 25.4 mm |

Conductor Related

| | |
|-----------------------------------|--|
| Conductor - Copper Str Size | 6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Str Size Range | 6 AWG-4/0 AWG |
| Conductor Type | CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Standards - RoHS Compliance Status | UI |

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)