



KPA34UNPL

by Burndy
Catalog ID: KPA34UNPL

Prop 65 Notice

Cu Unplated Terminal, 1 Hole, 4/0 Str-500 kcmil, 1/2" Stud, 1 Screw

Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	375
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810172742

Dimensions

Dimension - D inch	1.38 in
Dimension - Height fraction	2-7/16 in
Dimension - Height inch	2.44 in
Dimension - Hole Size inch	0.54 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	84 mm
Dimension - Length Overall inch	3.32 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch	1.38 in
Dimension - Stud Size inch	1/2

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)