



KPA4CG27

by Burndy
Catalog ID: KPA4CG27

Prop 65 Notice

Cu Terminal, For Cu Cable, 1 Hole, #14 - #4 AWG

Product Details

General

Connector Type	Terminal
Material	Copper
Material - Hardware	Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810172896
UPC 12 Digit	7818101728966

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - D inch	0.59 in
Dimension - Height fraction	47/50 in
Dimension - Height inch	0.94 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.19 in
Dimension - N inch	0.3 in
Dimension - Pad Width inch	0.50 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Navy Size	23 (7) Navy;30 (19) Navy;40 (19) Navy
Conductor - Copper Str Navy Size Range	23 (7) Navy-40 (19) Navy
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)