



KPA8CUPG10

by Burndy
Catalog ID: KPA8CUPG10

Copper Terminal, 1 Hole, 14 AWG (Sol)-6 AWG (Str), #10 Stud, 1 Screw;
Green Screw

Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	35
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810043981

Dimensions

Dimension - Height inch	0.81 in
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5.1 mm
Dimension - L Length Overall mm	26.4 mm
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	#10
Dimension - Width inch	0.38 in
Dimension - Width mm	9.4 mm

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Minimum Pack Quantity	2000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)