

KPB4CG1TN

by Burndy
Catalog ID: KPB4CG1TN

Prop 65 Notice

Terminal, Bolt Size: 5/16 IN, Conductor Range (Main/Primary): 10 - 4 AWG
Copper, Stud/bolt Hole Size: #10; Tin plated



Product Details

General

Installation Torque Recommended in-lb	45 LBS/in
Material	Copper Alloy
Material Type - Screw	Steel - Stainless
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810248782
UPC 12 Digit	7818102487822

Dimensions

Dimension - B Length inch	0.61 in
Dimension - Height inch	0.95 in
Dimension - Width fraction	1 in
Dimension - Width inch	0.99 in

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	<ul style="list-style-type: none">• UL467• UL 486A-B
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• UL 486A-B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)