



## KS15NK

by Burndy  
Catalog ID: KS15NK

Prop 65 Notice

Cu Alloy SERVIT Split Bolt, #10 Str. - #8 Sol.(Run), #14 - #8 AWG(Tap),  
Nickel Plated

## Product Details

### General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Nickel
Trade Name	SERVIT®
UPC	781810095584
UPC 12 Digit	7818100955844

### Dimensions

Dimension - Length Overall inch	0.85
Width	0.38 in

### Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Str Run Range	10 STR - 8 STR
Conductor - Copper Str Tap Range	10 STR - 8 STR
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Solid-Tap</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)