



## KS173RK

by Burndy  
Catalog ID: KS173RK

Prop 65 Notice

High copper alloy Split Bolt, SERVIT, Torque: 80 in-lb, Copper Conductor Stranded - Run Range: 10 - 8 Str

## Product Details

### General

Connector Type	Split Bolt
Installation Torque Recommended in-lb	165 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	SERVIT®
UPC	781810359990
UPC 12 Digit	7818103599900

### Dimensions

Dimension - B Length fraction	27/50 in
Dimension - B Length inch	0.54 in
Dimension - Cross Flats inch	0.62 in
Dimension - Length Overall inch	0.98 in
Dimension - Width fraction	7/10 in
Dimension - Width inch	0.7 in

### Conductor Related

Conductor - Copper Solid Tap	16 AWG; 15 AWG; 14 AWG; 13 AWG; 12 AWG; 11 AWG; 10 AWG; 9 AWG; 8 AWG; 7 AWG; 6 AWG
Conductor - Copper Solid Tap Range	16 AWG-6 AWG
Conductor - Copper Str Run	16 AWG; 14 AWG; 12 AWG; 10 AWG; 9 AWG; 8 AWG
Conductor - Copper Str Run Range	16 AWG-8 AWG

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	10
Packaging Type	Clamshell

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)