



KS17SV

by Burndy
Catalog ID: KS17SV

Prop 65 Notice

Cu Alloy SERVIT Split Bolt, #8 Str. - #6 Sol.(Run), #14 - #6 Str.(Tap), Silver Plated

Product Details

General

| | |
|----------------|---------------|
| Connector Type | Split Bolt |
| Material | Copper |
| Plated | Y |
| Plating Type | Silver |
| Trade Name | SERVIT® |
| UPC | 781810067697 |
| UPC 12 Digit | 7818100676977 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Length Overall inch | 1.14 |
| Width | 0.45 in |

Conductor Related

| | |
|----------------------------------|---------------|
| Conductor - Copper Solid Run | 6 AWG |
| Conductor - Copper Solid Tap | 6 AWG |
| Conductor - Copper Str Run Range | 8 STR - 6 STR |
| Conductor - Copper Str Tap Range | 8 STR - 6 STR |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)