



## KS20TN

by Burndy  
Catalog ID: KS20TN

Prop 65 Notice

Cu Alloy SERVIT Split Bolt, #8 - #4 AWG(Run), #14 - #4 AWG(Tap), Tin Plated

## Product Details

### General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810129081
UPC 12 Digit	7818101290811

### Dimensions

Dimension - Length Overall inch	1.2
Width	0.51 in

### Conductor Related

Conductor - Copper Solid Run	4 AWG
Conductor - Copper Solid Tap	4 AWG
Conductor - Copper Str Run Range	8 STR - 4 STR
Conductor - Copper Str Tap Range	8 STR - 4 STR
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Solid-Tap</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)