

KS20

by Burndy
Catalog ID: KS20

Prop 65 Notice

Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap), Length: 1.20.

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Type D Copperweld, Stranded Copperweld, Type A Copperweld, Installation Torque: 165 IN-LB, Length: 1.2 IN, Cross Flats: 0.69 IN, Width: 0.51 IN



Product Details

General

| | |
|-------------|---|
| Application | For Direct Burial Applications In Earth Or Concrete, Copper |
| Sub Brand | SERVIT |
| Type | KS, Compact |
| UPC | 781810012000 |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)