



KS22TN

by Burndy
Catalog ID: KS22TN

Prop 65 Notice

Cu Alloy SERVIT Split Bolt, #6 - #2 AWG(Run), #14 - #2 AWG(Tap), Tin Plated

Product Details

General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810094129
UPC 12 Digit	7818100941299

Dimensions

Dimension - Length Overall inch	1.5
Width	0.6 in

Conductor Related

Conductor - Copper Solid Run	2 AWG
Conductor - Copper Solid Tap	2 AWG
Conductor - Copper Str Run Range	6 STR - 3 STR
Conductor - Copper Str Tap Range	6 STR - 3 STR
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Str-Run • CU C Solid-Tap • CU C Str-Tap • CU Weld C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)