



KS23TN

by Burndy
Catalog ID: KS23TN

Prop 65 Notice

Cu Alloy SERVIT Split Bolt, #6 - #1 AWG(Run), #14 - #1 AWG(Tap), Tin Plated

Product Details

General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810054253
UPC 12 Digit	7818100542533

Dimensions

Dimension - Length Overall inch	1.54
Width	0.62 in

Conductor Related

Conductor - Copper Solid Run	1 AWG
Conductor - Copper Solid Tap	1 AWG
Conductor - Copper Str Run Range	6 STR - 2 STR
Conductor - Copper Str Tap Range	6 STR - 2 STR
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Str-Run • CU C Solid-Tap • CU C Str-Tap • CU Weld C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)