



KS23

by Burndy
Catalog ID: KS23

Prop 65 Notice

Copper Split Bolt, Cu: 6 AWG-2 AWG (Str) (Run & Tap).

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Type D Copperweld, Stranded Copperweld, Type A Copperweld, Installation Torque: 275 IN-LB, Length: 1.54 IN, Cross Flats: 0.82 IN, Width: 0.62 IN

Product Details

General

Application	For Direct Burial Applications In Earth Or Concrete, Copper
Connector Type	Split Bolt
Installation Torque Recommended in-lb	275 in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810012758
UPC 12 Digit	7818100127588

Dimensions

Dimension - B Length fraction	18/25 in
Dimension - B Length inch	.72 in
Dimension - Cross Flats inch	0.82 in
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.54
Dimension - Width fraction	31/50 in
Dimension - Width inch	0.62 in
Dimension - Width mm	16 mm
Width	0.62 in

Conductor Related

Conductor - Copper Solid Run	1 AWG
Conductor - Copper Solid Run Range	6 AWG-1 AWG
Conductor - Copper Solid Tap	1 AWG
Conductor - Copper Solid Tap Range	14 AWG-1 AWG
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG

Conductor - Copper Str Run Range	6 STR - 2 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Tap Range	6 STR - 2 STR
Conductor - CopperWeld Solid Run	#1
Conductor - CopperWeld Solid Run Range	#1
Conductor - CopperWeld Solid Tap	#1
Conductor - CopperWeld Solid Tap Range	#1
Conductor - CopperWeld Str Run	3 #7;3A;5D
Conductor - CopperWeld Str Run Range	3 #7-5D
Conductor - CopperWeld Str Tap	3 #7;3A;5D
Conductor - CopperWeld Str Tap Range	3 #7-5D
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)