



## KS25TN

by Burndy  
Catalog ID: KS25TN

Prop 65 Notice

Cu Alloy SERVIT Split Bolt, #4 - 1/0 (Run), #14 - 1/0 AWG(Tap), Tin Plated

## Product Details

### General

Connector Type	Split Bolt
Installation Torque Recommended in-lb	385 in
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810349243
UPC 12 Digit	7818103492433

### Dimensions

Dimension - Cross Flats inch	.94 in
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.77
Dimension - Width fraction	73/100 in
Dimension - Width inch	0.73 in
Dimension - Width mm	19 mm
Width	0.73 in

### Conductor Related

Conductor - Copper Solid Run	2/0 AWG
Conductor - Copper Solid Tap	2/0 AWG
Conductor - Copper Str Run Range	4 STR - 1/0 STR
Conductor - Copper Str Tap Range	4 STR - 1/0 STR
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul>

### Certifications and Compliance

Certification - UL Listed Direct Burial	Yes
---	-----

Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL 486A</li> <li>• UL486B</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL 486A</li> <li>• UL486B</li> </ul>
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)