



KS26NK

by Burndy
Catalog ID: KS26NK

Prop 65 Notice

Copper Split Bolt, Cu: 2 AWG-2/0 AWG (Str) (Run & Tap); Nickel Plated

Product Details

General

Connector Type	Split Bolt
Installation Torque Recommended in-lb	385 in
Material	Copper
Plated	Y
Plating Type	Nickel
Trade Name	SERVIT®
UPC	781810354797
UPC 12 Digit	7818103547977

Dimensions

Dimension - B Length inch	.90 in
Dimension - Cross Flats inch	1.05 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - Width fraction	41/50 in
Dimension - Width inch	0.82 in
Dimension - Width mm	21 mm

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)