



## KS29TN

by Burndy  
Catalog ID: KS29TN

Prop 65 Notice

Cu Alloy SERVIT Split Bolt, 4/0 Sol. - #1 Str.(Run), 250 kcmil - #8 Str. (Tap), Tin Plated

## Product Details

### General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810094105
UPC 12 Digit	7818100941055

### Dimensions

Dimension - Length Overall inch	2.25
Width	1 in

### Conductor Related

Conductor - Copper Solid Run	4/0 AWG
Conductor - Copper Solid Tap	4/0 AWG
Conductor - Copper Str Run Range	1 STR - 250 KCMIL
Conductor - Copper Str Tap Range	1 STR - 250 KCMIL

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	65
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)