



## KSU29

by Burndy  
Catalog ID: KSU29

Prop 65 Notice

Tin-plated, high strength copper alloy SERVIT with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors, 2.50 IN L.

Features: Tin-Plated, High Strength Copper Alloy SERVIT With Spacer, Spacer Separates Dissimilar Conductors And Provides Long Contact Length That Prevents High Pressure Point Contacts Between Run And Tap Conductors, Use Of PENETROX Joint Compound Recommended With Aluminum And ACSR, Installation Torque: 650 IN-LB, Conductor Type: Run: ACSR, 5005, AAAC, Commercial Stranded Aluminum, Commercial Stranded And Solid Copper, Tap: ACSR, 5005, AAAC, Commercial Stranded Aluminum, Commercial Stranded And Solid Copper, Steel (Nominal Diameter), Length: 2.5 IN, Width: 1.14 IN, Cross Flats: 1.38 IN

## Product Details

### General

Application	For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL SERVIT
Trade Name	SERVIT®
Type	KSU, Universal
UPC	781810036853

### Dimensions

Dimension - Length Overall inch	2.66
Width	1.22 in

### Conductor Related

Conductor - ACSR Str Run Range	2/0 AWG - 4/0 AWG
Conductor - ACSR Str Tap Range	6 AWG - 4/0 AWG
Conductor - AL Str Run Range	1 AWG - 250 KCMIL
Conductor - AL Str Tap Range	8 AWG - 250 KCMIL
Conductor - Copper Str Run Range	1 AWG - 250 KCMIL
Conductor - Copper Str Tap Range	8 AWG - 250 KCMIL

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)