



KVS26

by Burndy
Catalog ID: KVS26

Prop 65 Notice

Compact, two-piece, high strength, high copper alloy BURNDY OKLIP recommended for heavy duty connections. Neoprene rings hold DURIUM bolts in place during installation. Installed with ordinary wrench. Recommended tightening torque: 180 in-lb.

Features: Compact, Two-Piece, High Strength, High Copper Alloy BURNDY OKLIP Recommended For Heavy Duty Connections, Neoprene Rings Hold DURIUM Bolts In Place During Installation, Installed With Ordinary Wrench, Conductor Type: Run And Tap: Copperweld, Commercial Stranded Copper, Solid Copperweld, Installation Torque: 180 IN-LB, Conductor Spacer: No

Product Details

General

Application	For Copper, Copperweld
Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	OKLIP
Trade Name	OKLIP™
Type	KVS, Compact
UPC	781810061206
UPC 12 Digit	7818100612066

Dimensions

Dimension - Height inch	1.74 in
Dimension - Pad Width inch	1.06 in
Dimension - Stud Size inch	5/16 in
Dimension - Width inch	1.56 in
Dimension - Width mm	40 mm

Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-2/0 AWG
Conductor - Copper Str Run Range	1 str. 2/0 str.
Conductor - Copper Str Tap Range	6 str. - 2/0 str.
Conductor - CopperWeld Solid Run	3/0
Conductor - CopperWeld Solid Tap	3/0

Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap • CU Weld C Solid-Run • CU Weld C Solid-Tap
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)