



KVS28TN

by Burndy
Catalog ID: KVS28TN

Cast Cu Alloy Service Connector, 1/0 - 4/0 Str. (Run), #10 - 4/0 Str.(Tap),
Tin Plated

Product Details

General

Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	OKLIP™
UPC	781810503041
UPC 12 Digit	7818105030411

Dimensions

Dimension - Height inch	1.82 in
Dimension - Stud Size inch	3/8 in
Dimension - Width inch	1.67 in

Conductor Related

Conductor - Copper Str Run Range	1/0 str. - 4/0 str.
Conductor - Copper Str Tap Range	10 str. - 4/0 str.

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)