



KVSU34

by Burndy
Catalog ID: KVSU34

Prop 65 Notice

Tin-plated copper alloy connector with tin plated silicon bronze hardware. Spacer bar separates dissimilar conductors and provides long contact length, Tightening torque: 375 in -lb, wrench size: 3/4 cross flats.

Features: Compact, Tin Plated High Strength Copper Alloy Two-Piece Connector With Spacer And Tin-Plated Silicon Bronze DURUM Hardware, Recommended For Heavy Duty Connections, Spacer Separates Dissimilar Conductors And Provides Long Contact Length, Neoprene Ring Prevents Loss Of Shorter Bolt During Installation, Longer Peened Bolt Permits Swivel Action For Easier Installation, Use Of PENETROX Joint Compound Recommended With Aluminum And ACSR, Conductor Type: Run And Tap: Commercial Stranded Copper, Commercial Stranded Aluminum, ACSR, Solid Copper, 5005, Solid Copperweld, AAAC, Steel, Nominal Diameter, Stud/bolt Size: 1/2 IN, Installation Torque: 375 IN-LB, Length: 1-1/2 IN, Width: 2-1/4 IN, Height: 3 IN

Product Details

General

Application	For All Combinations Of Copper, Aluminum, ACSR, AAAC And 5005
Sub Brand	OKLIP
Type	KVS, Compact, Universal
UPC	781810083307

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)