



KVSU40W

by Burndy
Catalog ID: KVSU40W

Prop 65 Notice

Cast Cu Alloy Universal Service Connector, Silicon Bronze H/W, Hot Tin Dipped

Product Details

General

Material	Copper
Plated	Y
Plating Type	Hot Dip Galvanised
Trade Name	OKLIP™
UPC	781810353165
UPC 12 Digit	7818103531655

Dimensions

Dimension - Height inch	3.53 in
Dimension - Length Overall inch	1.62 in
Dimension - Stud Size inch	1/2 in
Dimension - Width inch	2.50 in

Conductor Related

Conductor - ACSR Str Run Range	336.4 kcmil-715.5 kcmil
Conductor - ACSR Str Tap Range	3/0 ACSR - 715.5 kcmil
Conductor - AL Str Run Range	400 kcmil- 800 kcmil
Conductor - AL Str Tap Range	4/0 str.- 800 kcmil
Conductor - Copper Str Run Range	400 kcmil- 800 kcmil
Conductor - Copper Str Tap Range	4/0 str. - 800 kcmil
Conductor - Galvanized Steel Str Run Range	3/4 in - 1 in
Conductor - Galvanized Steel Str Tap Range	1/2 in - 1 in
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • AL C Str-Tap • CU C Str-Run • CU C Str-Tap • AAAC C 5005-Run • AAAC C 5005-Tap • AAAC C 6201-Run • AAAC C 6201-Tap • ACSR C Str-Run • ACSR C Str-Tap • GAL Steel C Str-Run • GAL Steel C Str-Tap • Cu Weld Sol.- Run • Cu Weld Sol.- Tap

Certifications and Compliance

Standards - RoHS Compliance Status

CM

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)