



## KVS44TN

by Burndy  
Catalog ID: KVS44TN

Prop 65 Notice

Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Run: 500-1000 Kcmil, Tap: 250-1000 Kcmil.

## Product Details

### General

Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	OKLIP™
UPC	781810245934
UPC 12 Digit	7818102459344

### Dimensions

Dimension - Height inch	4.14 in
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	5/8 in
Dimension - Width inch	1.56 in

### Conductor Related

Conductor - Copper Str Run Range	500 kcmil- 1000 kcmil
Conductor - Copper Str Tap Range	250 kcmil - 1000 kcmil
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)