



LPHI10

by Burndy
Catalog ID: LPHI10

BURNDY; Hydraulic Intensifier; Pressure Rating: 10 M PSI, OPEN/CLOSED CENTER

Product Details

General

Tool Type	Low Pressure Hydraulic Intensifier
Type	Pumps
UPC	781810210659
UPC 12 Digit	7818102106599

Dimensions

Height	4.5 in
Length	5.25 in
Weight	9.75 lb
Width	4.25 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)