

LSC5561

by Burndy
Catalog ID: LSC5561

Prop 65 Notice

Cast Al Alloy Lightning Shield Clamp Assembly, 4/0 STR-556 AAC, 5.9 IN L, Galvanized Steel 3/8"-16 Eyebolt, insulation dia:1.34".

Features: Cast Aluminum Lightning Shield Clamp With A Galvanized Steel Eye Bolt For Use On Covered Aluminum And ACSR Primary Overhead Distribution Conductors (Tree Wire), They Are Designed To Protect The Tree Wire From Burn-Down Causing Service Interruption During High Lightning Activity, For Further Application Details Contact The Factory, Conductor Groove Is Pre-Filled With PENETROX A13, Which Is Compatible With Cable Insulation And Individually Bagged, Accommodates Cable Dia. a: 0.528 - 0.858 IN, Length: 5.9 IN



Product Details

General

Application	For Aluminum And ACSR Primary Covered Conductor (Tree Wire)
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Oxide Inhibitor Type	Penetrox A-13
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	CONNECTOR
Type	Arc Protection Device
UPC	781810084960

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.5 in
Dimension - L Length Overall mm	150 mm
Dimension - Length Overall inch	5.90 in

Conductor Related

Conductor - AL Str Size	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil
Conductor - AL Str Size Range	4/0 AWG-556 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	40
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)