



## LYM31C

by Burndy  
Catalog ID: LYM31C

Prop 65 Notice

WIRE: 350kcmil

## Product Details

### General

Connector Type	Limiter
Die Index	18
Insulation	Y
Insulation Type	Diatex
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	MOLIMITER™
UPC	781810000793
UPC 12 Digit	7818100007933

### Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Length Overall inch	14.25 in

### Conductor Related

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)