

# LYS28C

by Burndy  
Catalog ID: LYS28C

Prop 65 Notice

ACCOM: 4/0 STR



## Product Details

### General

Connector Type	Limiter
Die Index	15
Feature - Barrel Style	Tapered
Insulation	Y
Insulation Type	Rubber
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810175477
UPC 12 Digit	7818101754777

### Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Length Overall inch	16.25 in

### Conductor Related

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	4
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)