



M8ND

by Burndy
Catalog ID: M8ND

Prop 65 Notice

Full Cycle Ratchet Hand Crimping Tool, 26 AWG-8 AWG, N Dies.

Features: Fully Protected Ratchet Mechanism, Reinforced Heavy Duty Back, Long Handles Provide Greater Mechanical Advantages, Uses All Standard BURNDY N Dies, Easy Groove Identification With Colorcoded Dies, 5-year limited warranty, Width: 1-3/4 IN, Handle Length: 10-3/4 IN, Wire Stripper: No, Weight: 1.75 LB, Wire Cutter: No, Crimps Coaxial Connectors: No, Dieless: No

Product Details

General

Application	For 8 - 26 AWG Terminals And Splices
Sub Brand	HYTOOL
Trade Name	HYTOOL
Type	Crimpers
UPC	781810029817
UPC 12 Digit	7818100298177

Dimensions

Dimension - Length Overall inch	10.75 in
Dimension - Thread Size	-
Dimension - Width inch	1-3/4 in
Length	10.75 in

Conductor Related

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Aircraft Size Range	N/A
Conductor - Copper Str Size Range	N/A

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)